

Invizible™ Water Heater

IDEAL APPLICATIONS: Multi-Lavs, Kitchen Sink, Shower, Mop Sink, Scrub Sink, Eye/Face Wash

Invizible™ PRODUCT FEATURES

- Invizible™ wall sleeve conceals your Chronomite Heater inside the wall
- Chassis is ideally suited for new installations or for remodeling in masonry, tile, wood or other wall surfaces
- Series starts with 5-1/4" Depth Chassis allowing for standard wall depth installations
- 6 entry points to route electrical and water connections in any direction as needed per installation
- 4 bottom entry points constructed with knockouts for bulkhead and or sealed installation
- Slots in Chassis allow for different wall thicknesses and allow easy adjustment to align Wall Frame
- 1/4" mounting holes (Quantity 12 in chassis)
- Door/Frame (16 gage) and Chassis (20 gage) are fabricated from galvanized steel with a prime coat white finish
- Concealed Pivoting Rod Hinge prevents distortion and closes door squarely
- Pem Studs #8-32 are provided on chassis for easy mounting of R series heater
- Models with Electrical Disconnect are pre-wired for ease of installation
- Latch is screwdriver operated (Standard Models)
- Door Frame is one piece construction, 1" wide and provides perfect concealment of the rough wall opening
- Door has rounded safety corners
- Patent Pending



Z-R1414 Shown

GUIDE SPECIFICATION

Wall Sleeve shall be a Chronomite Laboratories Model

Z - _____

OPTIONS

Unit shall be fabricated from galvanized steel with a white prime coat finish suitable for painting. Access door shall have rounded safety corners and concealed pivoting rod hinge. Door/Frame 16 gage and wall sleeve 20 gage thickness. Latch shall be screwdriver operated. Wall Sleeve to have 10 entry points including 4 knockouts for bulkhead and or sealed installation.

OPTIONS

- -AKL Allen Key Latch
- -CL Cylinder Lock (one per door)
- -SS Stainless Steel Construction (Type 304 No. 4 Satin Finish)
- -SRK Semi Recess Kit

MODEL NUMBERS	NOMINAL SIZE	WALL OPENING	ELECTRICAL DISCONNECT
Z-R1414	14" x 14"	14-1/2" X 14-1/2" x 5-1/4"	NO
Z-R1818D	18" x 18"	18-1/2" X 18-1/2" x 6-1/4"	YES / PRE-WIRED

Complies with Standards for:


CHRONOMITE LABORATORIES, INC.

17451 Hurley St. :: City of Industry, CA 91744
Phone 800-447-4962 :: 626-937-4270
Fax 626-937-4279 :: www.chronomite.com

MEMBER OF



Invincible™ Water Heater



Complies
with
Standards
for:

CHRONOMITE LABORATORIES, INC.

17451 Hurley St. :: City of Industry, CA 91744
Phone 800-447-4962 :: 626-937-4270
Fax 626-937-4279 :: www.chronomite.com

MEMBER OF



Invizible™ Water Heater

R Series Heater

GUIDE SPECIFICATION

Tankless Water Heater shall be a Chronomite Laboratories Model

R - _____ **L /** _____
AMPS VOLTS

OPTIONS

with _____ Amps and _____ Volts

Unit shall be provided with Celcon waterways, and Nichrome heating coils.
Temperature controlled by microprocessor.

OPTIONS

- ☐ Factory Preset (F)
- ☐ Satin Stainless Steel Housing (SS)
- ☐ Disconnect Switch, Rotary 80A-Lockable NEMA 4X (2095-4) (Shipped Loose)
- ☐ Noise Suppression Relay (Q)
- ☐ Digital Readout (DR)

For the model being selected, please place the corresponding amps and volts values in the Guide Specifications above.

MODEL	AMPS	VOLTS	WATTS	ACTIVATION GPM	TEMP RISE @ 1.5 GPM	TEMP RISE @ 2.5 GPM	TEMP RISE @ 3.0 GPM
R-48L / 208	48	208	10000	0.35	45	27	23
R-48L / 240	48	240	11500	0.35	52	31	26
R-58L / 208	58	208	12050	0.35	55	33	27
R-63L / 208	63	208	13100	0.35	60	36	30
R-48L / 277	48	277	13300	0.35	61	36	30
R-58L / 240	58	240	13900	0.35	63	38	32
R-68L / 208	68	208	14150	0.35	64	39	32
R-63L / 240	63	240	15100	0.35	69	41	34
R-75L / 208	75	208	15600	0.35	71	43	36
R-58L / 277	58	277	16050	0.35	73	44	37
R-68L / 240	68	240	16300	0.35	74	45	37
R-63L / 277	63	277	17450	0.35	79	48	40
R-75L / 240	75	240	18000	0.35	82	49	41
R-68L / 277	68	277	18850	0.35	86	51	43
R-75L / 277	75	277	20750	0.35	95	57	47

Chronomite Laboratories assumes no responsibility for use of void or suspended data. © Copyright Chronomite Laboratories, Inc.
Member of Morris Group International, City of Industry, CA Please visit www.chronomite.com for most current specifications.

SELECTION SUMMARY & APPROVAL FOR MANUFACTURING	Company _____	
	Model Number & Options _____	Quantity _____
	Contact _____	Title _____
	Signature (Approval for Manufacturing) _____	
	Date _____	

CHRONOMITE
LABORATORIES, INC.
PH. 800-447-4962
626-937-4270
FAX 626-937-4279
www.chronomite.com