




NOTE: USE ONLY APPROPRIATE UPC/cUPC CERTIFIED FLUSH VALVE FOR THE INSTALLATION OF THIS URINAL.



SIDE VIEW



**REAR VIEW
-W WALL SUPPLY UNIT**



**ROUGH-IN REAR VIEW OF
-T TOP SUPPLY UNIT**

INSTALLATION INSTRUCTIONS:

- A- ROUGH-IN FOR THE FOLLOWING:
 - 3/4" NPT FLUSHING INLET (1). (MALE ADAPTER WITH FLEXIBLE HOSE PROVIDED FOR -W WALL SUPPLY MODELS, DETAIL "A").
 - 3/4" NPT EXISTING FLUSH VALVE INLET (2) WHEN -FV FLUSH VALVE IS PROVIDED.
 - WASTE OUTLET 1-1/2" PLAIN END (3).
- B- FOR EXISTING DURA-WARE FLUSH VALVE ACCESS PANELS (4), FOR CONCEALED FLUSH VALVE PANELS CONTACT FACTORY.
- C- FASTEN 1/2"-13 UNC ALL-THREAD STUDS (5) PROVIDED, TO FIXTURE MOUNTING POINTS (6) AND SLIDE STUDS (5) THRU WALL OPENINGS. NOTE: STUDS MUST HAVE A 1/2" ENGAGEMENT MIN.
- D- FROM CHASE SIDE SECURE FIXTURE USING WASHERS (7) & NUTS (8) PROVIDED.
- E- MAKE UP WASTE CONNECTION (3).

- F- **FOR OPTIONAL -FV FLUSH VALVE:**
 - CONNECT FLUSH VALVE AS REQUIRED FOR EXPOSED (9) OR CONCEALED (10) INSTALLATION PER MANUFACTURERS' RECOMMENDATIONS. -W WALL SUPPLY FLUSH VALVE, ACCESS FOR CONNECTION AND SERVICING FLUSH VALVE IS REQUIRED.
- NOTE:**
FOR SUFFIX OPTION -ADA UNITS, REFER TO ADA ACCESSIBILITY GUIDELINES FOR COMPLETE INSTALLATION REQUIREMENTS. ALL VERTICAL DIMENSIONS INDICATED **DECREASE PROPORTIONATELY WITH ADA RIM HEIGHT: FOR ADA RIM HEIGHT OF 17", WASTE OUTLET BECOMES 13" AFF.
- 1-ADA FLUSH VALVE MUST BE HYDRAULICALLY ACTUATED OR SUPPLIED WITH A SPECIAL HANDLE. MAXIMUM CONTROL HEIGHT IS 44" ABOVE FINISHED FLOOR.
 - 2-ADA REQUIRES A RIM HEIGHT OF 17" MAXIMUM AFF.

<p>ACORN ENGINEERING COMPANY P.O. BOX 3527 Industry, CA 91744 15125 Proctor Ave Industry, CA 91746 (626) 336-4561 FAX (626) 961-2200</p>	<p>TITLE HEU REPLACEMENT URINAL, #3346 (FOR #1705)</p>		
	<p>MANUFACTURE DATE SEPTEMBER 2016 TO PRESENT</p>	<p>DATE ISSUED 09/26/16</p> <p>DATE REVISED</p>	<p>DRAWING NUMBER 9925-744-001</p>