

DRAWING NUMBER  
**S0375**

SIZE  
**A**

SCALE:  
**NONE**

DATE:

APPROVED BY:

CHECKED BY:

DRAWN BY:

**0375**


FIGURE NUMBER

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA


DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCE AND CHANGE WITHOUT NOTICE

## ADJUSTABLE FIXTURE SUPPORTS FOR ELEVATED BLOWOUT WATER CLOSETS FOR WHEELCHAIR USERS


### VERTICAL FITTING WITH SIDE INLET



**Fig. 0375L Side View**



**Fig. 0375D Side View**



**Front View**

- Fig. 0375L . . . CAULK Left Hand Long Barrel
- Fig. 0375R . . . CAULK Right Hand Long Barrel
- Fig. 0375D . . . CAULK Double Long Barrel

- NOTE:** Base support must be firmly anchored to floor with four 1/2"(13) bolts provided by contractor.
- NOTE:** When used with concealed flush valve locate face plate behind supply pipe.
- NOTE:** 1 1/2(38) or 2"(51) tapped inlet available add suffix -N.

AxB SIZE	D		J	K	L	M	S
	MIN	MAX					
4x4 (100) x (100)	4 3/4 (120)	8 3/4 (220)	12 1/8 (308)	7 1/2 (190)	3 (76)	7 (180)	5 1/4 (135)


The water closet outlet gasket regularly furnished is made of molded neoprene and designed to fit water closet outlet dimensions and configurations shown in ANSI Standard A112.19.2M-1995, Figure 13B. If gasket is not found to be compatible to fixture due to nonconformance of said fixture to ANSI A112.19.2M, then fixture manufacturer shall be consulted for a suitable gasket recommendation. Jay R. Smith assumes no liability for connections to fixtures which do not conform to these standards.

Conforms to ASME A112.61M.

### Ⓢ DIMENSION - ADJUS-TO-WALL TYPE OUTLET CONNECTION

The Smith Adjus-to-Wall outlet connection provides adjustment at the face of the wall at the time the fixture is set; thus, compensating for wall construction variations. The Ⓢ dimension is measured from the front of the face plate to the finished wall. To properly determine the length of nipple required, deduct 1" (25) from the Ⓢ dimension. When the Ⓢ dimension exceeds 7" (180), the -M40 Wide Pipe Chase Support is recommended. The Adjus-to-Wall coupling will provide 1/2" (13) horizontal adjustment in either direction with the coupling extended 5/16" (8) past face of the finished wall.

Ⓢ dimension = 4" (100) (regularly furnished) consisting of nipple and Adjus-to-Wall coupling permitting adjustment from 3" (76) min. to 4" (100) max.



### NIPPLE LENGTHS AVAILABLE

LENGTH	MIN	Ⓢ	MAX
2 1/2 (64)	2 1/4 (57)	3 1/4 (83)	
*3 1/4 (83)	3 (76)	4 (100)	
*8 1/4 (210)	8 (205)	9 (230)	
10 (255)	9 3/4 (250)	10 3/4 (275)	
12 (305)	11 3/4 (300)	12 3/4 (325)	
15 (380)	14 3/4 (375)	15 3/4 (400)	
18 (455)	17 3/4 (450)	18 3/4 (475)	

**NOTE:** When nipple lengths between 3 1/4" (83) and 8 1/4" (210) are specified, the 8 1/4" (210) nipple will be supplied. Nipple must be cut to specified length by others.

\*ABS (Regularly Furnished) other lengths PVC.

**NOTE:** Dimensions shown in parentheses are in millimeters.

J H G F	4-16-24 2-2-24 7-1-98 1-23-98	Added ASME Note Rev. Adjus-to-Wall, Ⓢ Submittal Update Added Millimeters	HS HS ASL EMB	CL CL BS BS	WEIGHT POUNDS	VOLUME CUBIC FEET	<b>0375</b>
REV.	DATE	DESCRIPTION	BY	CKD. BY			